


FD 23 - Drying oven with forced convection

FD series units are primarily used in applications needing rapid drying and sterilization. Totally homogenous temperature distribution, rapid dynamic response, and a special air turbine which was developed by us and has 20 % higher output, have made the FD series a genuine time-saving device.



▶ Performance features and equipment :

- Electronically controlled APT.line™ preheating chamber assuring temperature accuracy and reproducible results
- Temperature range 5 °C (32 °F) above ambient temperature up to 300 °C (572 °F)
- DS controller with integrated timer 0 to 99 h
- Digital temperature setting with an accuracy of one degree
- Independent adjustable temperature safety device class 2 (DIN 12880), with visual temperature alarm
- Adjustable front ventilation flap slide and rear exhaust ø 50 mm (1.97 inch)
- Units up to 115 liters are stackable
- 2 chrome-plated racks included
- BINDER test certificate



FD 23

| Exterior dimensions | |
|---|------------|
| Width (mm/inch) | 433 / 17.1 |
| Height (inclusive feet/castors) (mm/inch) | 492 / 19.4 |
| Depth (mm/inch) | 516 / 20.3 |
| Plus door handle, I-panel and exhaust duct (mm/inch) | 85 / 3.4 |
| Wall clearance rear (mm/inch) | 100 / 3.9 |
| Wall clearance side (mm/inch) | 100 / 3.9 |
| Exhaust duct outer- Ø (mm/inch) | 52 / 2.1 |
| Steam space volume (l/cu.ft.) | 36 / 1.3 |
| Number of doors | 1 |
| Interior dimensions | |
| Width (mm/inch) | 222 / 8.7 |
| Height (mm/inch) | 330 / 13.0 |
| Depth (mm/inch) | 277 / 10.9 |
| Interior volume (l/cu.ft.) | 20 / 0.7 |
| Racks, chrome-plated (number standard/max.) | 2 / 3 |
| Load per rack (kg/lbs.) | 12 / 26 |
| Permitted total load (kg/lbs.) | 25 / 55 |
| Weight of the unit (empty) (kg/lbs.) | 33 / 73 |
| Temperature data | |
| Temperature range, 5 °C (41 °F) above ambient up to (°C / °F) | 300 / 572 |
| Temperature variation 1) | |
| at 70 °C (± °C) | 0.8 |
| at 150 °C (± °C) | 2.2 |
| at 300 °C (± °C) | 4.3 |
| Temperature fluctuation (± °C) | 0.3 |
| Heating up time 1), 2) | |
| to 70 °C (Min.) | 7 |
| to 150 °C (Min.) | 22 |
| auf 300 °C (Min.) | 45 |
| Recov. time after door was opened for 30 sec. | |
| at 70 °C (Min.) | 2 |
| at 150 °C (Min.) | 4 |
| at 300 °C (Min.) | 9 |
| Air change data | |
| Air change | |
| at 70 °C (x/h) | 59 |
| at 150 °C (x/h) | 64 |
| at 300 °C (x/h) | 53 |
| Electrical data | |
| Housing protection acc. to EN 60529 | IP 20 |
| Nominal voltage (±10 %) 50 / 60 Hz (V) | 230 / 115 |
| Nominal power (kW) | 0.8 |
| Energy consumption | |
| at 70 °C (W) | 145 |
| at 150 °C (W) | 300 |
| at 300 °C (W) | 720 |

1) value without window
2) up to 98 % of the set value

All technical data are specified for units with standard equipment at an ambient temperature of 25 °C and a voltage fluctuation of ±10 %. The temperature data are determined in accordance to factory standard following DIN 12880 respecting the recommended wall clearances of 10 % of the height, width and depth of the inner chamber. All indications are average values, typical for units produced in series. We reserve the right to alter technical specifications at all times.



▶ Access ports

With silicon plugs for inserting external measuring devices into the chamber. Access ports with 10, 30, 50 mm (0.4, 1.2, 2 inch) diameter.



▶ Door with window and interior lighting

For optimum process control in the interior, available for all equipment sizes.



▶ Lockable door

Prevents unauthorized access and interference with processes in the chamber.



▶ Calibration certificates and validation

BINDER can significantly reduce the time and effort needed for equipment qualification. We draw on unparalleled knowledge of our equipment applications and years of experience in certification.



FD 23

| | |
|--|-----------------------|
| Access port with silicone plugs, 10 mm (0.39 inch), 30 mm (1.18 inch), 50 mm (1.97 inch) | <input type="radio"/> |
| Independent adjustable temperature safety device, Class 3.1 (DIN 12880) | <input type="radio"/> |
| Analog temperature output, 4 - 20 mA, with 6 - pin DIN socket (output not adjustable) | <input type="radio"/> |
| Over temperature alarm, acoustic, can be switched off. Temperature limit can be set at the independent, adjustable temperature safety device class 2 | <input type="radio"/> |
| Temperature measurement acc. to DIN 12880 (27 measuring points) at 150 °C (302 °F) or at specified temperature with measuring protocol and certificate | <input type="radio"/> |
| Factory calibration certificate. Measurement in center of chamber at 150 °C (302 °F) or at specified testing temperature | <input type="radio"/> |
| Extension to factory calibration certificate. Each additional measurement at an additional measuring point or temperature | <input type="radio"/> |
| Rack, chrome - plated or stainless steel | <input type="radio"/> |
| Shelf, perforated, stainless steel | <input type="radio"/> |
| Lockable door | <input type="radio"/> |
| FKM door gasket | <input type="radio"/> |
| Door with window and interior lighting, 15 W (180 x 180 mm / 7.09 x 7.09 inch) | <input type="radio"/> |



Thank you for reading this data sheet.

For pricing or for further information, please contact us at our UK Office, using the details below.



UK Office

Keison Products,

P.O. Box 2124, Chelmsford, Essex, CM1 3UP, England.

Tel: +44 (0)330 088 0560

Fax: +44 (0)1245 808399

Email: sales@keison.co.uk

Please note - Product designs and specifications are subject to change without notice. The user is responsible for determining the suitability of this product.