

Data Sheet

Mixing / Overhead Stirrers



EUROSTAR 100 control

Powerful laboratory stirrer designed with a removable wireless controller and a digital TFT display. It automatically adjusts the speed through microprocessor controlled technology within the speed range of 0/30 - 1300 rpm. The stirrer comes equipped with a RS 232 and a USB interface to control and document all parameters. An integrated torque trend display is provided for the measurement of viscosity changes. Safety circuits installed ensures automatic cut-off in an anti-stall or overload conditions. Continuous comparison of shaft speed to desired speed is maintained and variations are adjusted automatically. This guarantees a constant speed even with changes in viscosities of the sample.

- Multilingual TFT display
- Programmable functions
- Integrated temperature measurement
- Interval operation
- Reverse function
- Timer function
- Adjustable safety circuit
- Locked function
- Infinitely adjustable speed
- Push-through agitator shafts
- Overload protection
- Short-term overload operation
- Quiet operation
- Error code display

Accessories: R 1342 Propeller stirrer, 4-bladed, R 1345 Propeller stirrer, 4-bladed, R 1381 Propeller stirrer, 3-bladed, R 1382 Propeller stirrer, 3-bladed, R 1385 Propeller stirrer, 3-bladed, R 1388 Propeller stirrer, 3-bladed, R 1389 (PTFE-coated) Propeller stirrer, 3-bladed, R 1311 Turbine stirrer, R 1312 Turbine stirrer, R 1313 Turbine stirrer, R 1300 Dissolver stirrer, R 1302 Dissolver stirrer, R 1303 Dissolver stirrer, R 1352 Centrifugal stirrer, R 1355 Centrifugal stirrer, R 1375 Paddle stirrer, R 1376 Paddle stirrer, R 1330 Anchor stirrer, R 1331 Anchor stirrer, R 1333 Anchor stirrer, H 66.53 Temperature sensor, coated, H 62.51 Stainless steel sensor, H 66.51 Stainless steel sensor, glass-coated, H 70 Extension cable, R 60 Keyless chuck, R 301 Stirring shaft protection, R

Technical Data	
Stirring quantity max. (H ₂ O) [l]	100
Motor rating input [W]	174
Motor rating output [W]	142
Motor principle	Brushless DC
Speed display	TFT
Speed range [rpm]	0/30 - 1300
Reversible direction of rotation	yes
Intermittent operation	yes
Viscosity max. [mPas]	70000
Output max. at stirring shaft [W]	136
Permissible ON time [%]	100
Torque max. at stirring shaft [Ncm]	100
Speed control	stepless
Setting accuracy speed [±rpm]	1
deviation of speed measurement n > 300rpm [±rpm]	3
deviation of speed measurement n < 300rpm [±%]	1
Stirring element fastening	chuck
Connection for ext. temperature sensor	PT1000
Temperature display	yes
Chuck range min. diameter [mm]	0.5
Chuck range max. diameter [mm]	10
Hollow shaft, inner diameter [mm]	11
Hollow shaft (push-through $\varnothing$ when stopped)	yes
Fastening on stand	extension arm
Extension arm diameter [mm]	16
Extension arm length [mm]	220
Torque display	yes
Nominal torque [Nm]	1
Torque measurement	trend
deviation of torque measurement I [±Ncm]	6
Timer	yes
Timer display	TFT
Time setting range [min]	1 - 6000
Temperature measuring range min. [°C]	-10
Temperature measuring range max. [°C]	+350
Temperature measurement resolution [K]	0.1
Accuracy of temperature measurement [K]	±0.5 + tolerance PT1000 (DIN IEC 751 Class A)
Limit deviation temperature sensor [K]	≤ ± (0.15 + 0.002x T)
housing material	alu-cast coating / thermoplastic polymer
clean room qualified	no
explosion proofed	no
communication distance (depend on building) max. [m]	150
Dimensions (W x H x D) [mm]	86 x 267 x 230
Weight [kg]	4.7
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 40
RS 232 interface	yes
USB interface	yes
Analog output	no
Voltage [V]	230 / 115 / 100 - 115 / 100
Frequency [Hz]	50/60
Power input [W]	186
Ident. No.	0004028500

270 Boss head clamp, R 271 Boss head clamp, RH 5 Strap
clamp, R 2722 H-Stand, R 2723 Telescopic stand,
labworldsoft®



Thank you for reading this data sheet.

For pricing or for further information, please contact us at our UK Office, using the details below.



UK Office

Keison Products,

P.O. Box 2124, Chelmsford, Essex, CM1 3UP, England.

Tel: +44 (0)330 088 0560

Fax: +44 (0)1245 808399

Email: sales@keison.co.uk

Please note - Product designs and specifications are subject to change without notice. The user is responsible for determining the suitability of this product.