

Data Sheet

Mixing / Magnetic Stirrers



RO 15

The 15-position digital magnetic stirrer without heating, designed for synchronous stirring. The magnetic

coil technology provides noiseless and consistent stirring on all positions. Speed remains constant, even when load changes. The closed and compact design allows easy cleaning and protects the equipment against the penetration of liquids. Additionally, a removable transparent anti-slip mat is included.

- Adjustable reverse operation
- Wear free magnetic coils
- Error Code Display
- Easy operation with touch keypad
- Suitable for continuous operation
- Adjustable speed in increments of 10 rpm

Accessories: IKAFLON® 15 Set (5 Pcs) power SmSo PTFE-coated Magnetic stirring bars, TRIKA® 25 Set (5 Pcs) PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 10 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 15 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) round

Technical Data	
Number of stirring positions	15
Stirring quantity max. per stirring position (H2O) [I]	0.4
Stirring position distance [mm]	90
Speed deviation of individual stirring positions [%]	0
Stirring quantity max. (H2O) [I]	6
Speed display	LED line
Speed range [rpm]	0 - 1200
Stirring bar length max. [mm]	30
Speed control	10 RPM Steps
Set-up plate material	stainless steel 1.4301
Set-up plate dimensions [mm]	280 x 470
Dimensions (W x H x D) [mm]	280 x 60 x 570
Weight [kg]	7
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 40
Voltage [V]	100 - 240
Frequency [Hz]	50/60
Power input [W]	40
DC Voltage [V=]	24
Current consumption [mA]	1500
Ident. No.	0003692500
·	

PTFE-coated Magnetic stirring bars, IKAFLON® glass 25 Set (5 Pcs) round Magnetic stirring bars, IKAFLON® glass 30 Set (5 Pcs) round Magnetic stirring bars, IKAFLON® 9 Set (5 Pcs) crown PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) power SmSo PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 10 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, H 11 Mains cable CH plug, H 11 Mains cable USA plug, H 11 Mains cable Euro plug, RSE Stirring bar remover, H 11 Mains cable UK plug



Thank you for reading this data sheet.

For pricing or for further information, please contact us at our UK Office, using the details below.

::: UK Office Keison Products,

P.O. Box 2124, Chelmsford, Essex, CM1 3UP, England.

Tel: +44 (0)330 088 0560

Fax: +44 (0)1245 808399 Email: sales@keison.co.uk

Please note - Product designs and specifications are subject to change without notice. The user is responsible for determining the suitability of this product.