

## Key Features

- Wavelength range of 198 to 1000nm
- Xenon lamp
- Easy and intuitive operation
- Absorbance, %T and concentration modes
- Multi-parameter display with wavelength and photometric readouts
- Wide range of sampling accessories
- 3 year warranty



6305

Part code: 635 001

6305

## UV/Visible Spectrophotometer

The 6305 is ideal for applications similar to the 6300 requiring measurements in the UV and visible wavelength ranges. Using a single, pulsed xenon lamp the 6305 offers an extended lamp life and high energy throughput in the UV and visible regions.

### Technical Specification

#### Wavelength

Range	198 to 1000nm
Resolution	1nm
Accuracy	±2nm
Spectral bandwidth	8nm, 6nm over UV range

#### Photometrics

Transmittance	0 to 199.9%T
Absorbance	-0.300 to 1.999A
Accuracy	±1%T
Resolution	0.1%T, 0.001A
Stray light	<0.5%T at 220 and 340nm
Noise	<0.001A at 0A at 400nm
Stability	<0.002A/h after 30 minutes

#### Concentration

Range	-300 to 1999
Resolution	0.1 to 1
Units	ppm, mg/l, g/l, M, %, blank
Factor	0 to 199.9, 1000 to 9999

#### Other

Light source	Xenon lamp
Outputs	Analogue and RS232
Power	<50W*
Size (w x d x h), mm	365 x 272 x 160
Weight, kg	6

### Ordering Information

Part Code	Description
635 001	6305 UV/Visible spectrophotometer supplied with mains lead, pack 100 disposable cuvettes, 10x10mm cell holder, interface cable and 63-Zero PC application software on CD-ROM** (230/50Hz)

\* Voltage variants available see page 94

\*\* Requires free on-line registration



Thank you for reading this data sheet.

For pricing or for further information, please contact us at our UK Office, using the details below.



**UK Office**

**Keison Products,**

**P.O. Box 2124, Chelmsford, Essex, CM1 3UP, England.**

**Tel: +44 (0)330 088 0560**

**Fax: +44 (0)1245 808399**

**Email: [sales@keison.co.uk](mailto:sales@keison.co.uk)**

Please note - Product designs and specifications are subject to change without notice. The user is responsible for determining the suitability of this product.