

D4000

Water Stills, Distinction

All glass construction with silica sheathed heaters ensures top purity distillate at an economical price. Fitted with a control device to turn off the heater when the collecting reservoir is full. Prevents overflow if the still is inadvertently left switched on when unattended. With two independent safety thermostats to prevent over heating in the event of an interruption to the water supply.

The unique condenser design ensures that the droplets of distilled water remain in contact with the cooling coil for the longest possible time producing cold distilled water and pre-heating the boiler feed to increase efficiency. Screwthreads are incorporated on all water connections so hoses can be fitted and removed easily and safely without risk of breakage. Built in acid addition funnel and drain stopcock allow easy descaling without dismantling the glassware. The stand is pre-drilled to facilitate wall mounting.

Technical Specification

Output	4 litres/hr, single distilled
pH	5.0 – 6.5
Conductivity, μScm^{-1}	1.0 – 2.0
Resistivity, $\text{mOhm}\cdot\text{cm}$	0.5 – 1.0
Temperature	25 - 35°C
Pyrogen content*	Pyrogen free
Water supply	1 litre/min 3 – 100psi (20-700kPa)
Electricity supply phase	220 or 240V, 50-60Hz, single phase
Power requirement	3kW
Dimensions, mm (w x d x h)	540 x 160 x 410
IP Rating	31

* care is required to produce pyrogen free water and the output should be tested before use.

Ordering Information

Model	Description
D4000	Distinction water still, 240V
D4000/EURO	Distinction water still, 220V

Conductivity and resistivity are affected by the presence of dissolved carbon dioxide. All figures given in this catalogue are based on tests carried out on the still output at 20°C and free from carbon dioxide.

Key Features

- All glass construction
- Two independent safety thermostats
- Safety reservoir full shut off
- Wall mountable
- Silica sheathed heaters

D4000





Thank you for reading this data sheet.

For pricing or for further information, please contact us at our UK Office, using the details below.



UK Office

Keison Products,

P.O. Box 2124, Chelmsford, Essex, CM1 3UP, England.

Tel: +44 (0)330 088 0560

Fax: +44 (0)1245 808399

Email: sales@keison.co.uk

Please note - Product designs and specifications are subject to change without notice. The user is responsible for determining the suitability of this product.